

CLEANING SOLUTIONS

B-Clean by Bollé Safety is a complete and efficient cleaning solutions range. Silicone free, its aqua formula guarantees perfect cleaning and protection for your glasses and goggles.



Cleaning Sprays



B402
PACS500



B411
PACS250



B412
PACS050

Wipes & Tissues



B500
PACW500



B100
PACW100



B401
PACMPCT

Anti-fog Sprays



B200
PACF030



B250
PACF500



B300
PACFAR3

Dispensers



B600
PACD500



B410
PACD250

+ AQUA FORMULA

+ SILICONE FREE

+ FOR ALL TYPES OF LENSES*

(* EXCEPT AR COATED LENSES FOR THE PACF030 & PACF500 VERSIONS)

bolle
SAFETY

CLEANING SOLUTIONS

PRODUCT	REF.	DESCRIPTION	DIMENSIONS IN CM	WEIGHT IN GR
Cleaning Sprays				
B402	PACS500	Lens cleaner (spray) 500ml	H: 22.5 x Ø: 6,5	540g
B411	PACS250	Lens cleaner (spray) 250ml	H: 19 x Ø: 5	270g
B412	PACS050	Lens cleaner (spray) 50ml	H: 11,3 x Ø: 3,2	60g
Anti-Fog Sprays				
B250	PACF500	Anti-fog (spray) 500ml	H: 22.5 x Ø: 6,5	540g
B200	PACF030	Anti-fog kit: 30ml anti-fog solution (spray) + microfiber tissue included	H: 13.5 x L: 5 x P: 3.5	90g
B300	PACFAR3	Anti-fog kit: 30ml anti-fog solution (spray) + synthetic shammy cloth included	H: 11 x L: 4 x P: 3.5	58g
Cleaning Wipes & Tissues				
B500	PACW500	500 cleaning premoistened tissues dispenser	H: 22 x L: 27.5 x P: 10.5	1300g
B100	PACW100	100 cleaning premoistened tissues dispenser	H: 20.5 x L: 12.5 x P: 6	290g
B401	PACMPCT	200 multi-function dry cleaning tissues for PACD500 & PACD250	H: 12 x L: 16 x P: 5	155g
Dispensers				
B600	PACD500	Plastic cleaning station with 500ml lens cleaner + 2 x 200 multi-function dry cleaning tissues	H: 34.5 x L: 45 x P: 7.5	1565g
B410	PACD250	Carton cleaning station with 250ml lens cleaner + 2 x 200 multi-function dry cleaning tissues	H: 16.5 x L: 29.5 x P: 5.5	680g

See user instructions on the next page.

PACKAGING AND EAN 13 CODE

	PACS500	PACS250	PACS050	PACF500	PACF030	PACFAR3	PACW500	PACW100	PACMPCT	PACD500	PACD250
Per piece	3660740009892	3660740009915	3660740009922	3660740009878	3660740009861	3660740011949	3660740009939	3660740009854	3660740009885	3660740008741	3660740009908
Quantity per inner box	-	-	-	15	10	10	-	25	-	-	10
Quantity per master carton	27	28	91	30	100	100	12	50	36	6	20



Non-contractual pictures

10/05/2021

Bollé Safety AU Pty Limited
32-40 Fairchild Street
Heatherton VIC 3202
T: 1300 138 098
E: sales@bollesafety.com.au

Hong Kong Bollé Safety
818, 8/F, Ocean Centre, Harbour City,
5 Canton Road, Tsim Sha Tsui,
Kowloon, Hong Kong
T.: +852 2732 5038

bollesafety.com.au

bolle
SAFETY

CLEANING SOLUTIONS

USER INSTRUCTIONS

PRODUCT	SKU	USER INSTRUCTION
Anti-fog	PACF030* PACF500*	Remove the glasses from your face. Spray anti-fog solution on both sides of your glasses and dry it with a microfibre cloth. After applying the anti-fog spray wait 2 minutes before wearing the glasses.
Anti-Fog	PACFAR3	Remove the glasses from your face. Spray anti-fog solution on both sides of your glasses and dry it using the synthetic shammy cloth. After applying the anti-fog spray wait 2 minutes before wearing the glasses.
Cleaning Tissues	PACW100 PACW500	Remove the glasses from your face. Unfold a cleaning premoistened tissue and use it to gently clean both sides of your lenses in circular movements until it is dry.
Cleaning Sprays	PACD250 PACD500 PACS050 PACS250 PACS500	Remove the glasses from your face. Spray cleaning solution on both sides of your glasses and dry it with a microfibre cloth.

* Do not use PACF500 & PACF030 on anti-reflect coated equipments.

STORAGE: All products must be stored in a dry and clean environment.



Non-contractual pictures

10/05/2021

Bollé Safety AU Pty Limited
32-40 Fairchild Street
Heatherton VIC 3202
T: 1300 138 098
E: sales@bollesafety.com.au

Hong Kong Bollé Safety
818, 8/F, Ocean Centre, Harbour City,
5 Canton Road, Tsim Sha Tsui,
Kowloon, Hong Kong
T.: +852 2732 5038

bollesafety.com.au

bolle
SAFETY